

Why the SANS SHS-100 headset is Superior to less expensive Knock Offs

September 16, 2013

Aren't they all the same? **Absolutely NOT!**



SANS (SHS-100)



Sanako (SLH-07)



Robotel (SC2500)



ReLanPro

SANS has taken the initiative to request and oversee the implementation of several critical improvements in the design and construction of our SHS-100 headset to ensure a better user experience and reliability in high traffic educational settings.

To summarize some key differences:

- A cotton thread has been added in the cord to provide added strain relief when the cord gets stretched or pulled.
- A new RJ45 plug with an "M" shaped blade is used to add additional strain relief and increase the secure crimping.
- The gold plating is now 6p6c 15U (thicker plating – less likely to wear down and cause static).



The gold plating is now 6p6c 15U (thicker plating – less likely to wear down and cause static).

A new RJ45 plug with an "M" shaped blade is used to add additional strain relief and increase the secure crimping.

A cotton thread has been added in the cord which will provide added strain relief when the cord gets stretched or pulled.



So, while they may look similar – that is where the similarity ends. **Do not allow your potential customers think we are providing anything less than a headset that is superior in construction and sound quality.**